

# USB-CTR Series

## High-Speed Counter/Timer Devices with Digital I/O



### Features

- High-speed pulse counter for general counting applications
- Available in 8-channel and 4-channel models
- 48 MHz maximum input frequency
- Programmable resolution up to 64-bits
- Aggregate scan rate of 8 MB/s
- Supports the following counter input modes:
  - Totalize (event counting)
  - Period measurements
  - Pulse-width measurements
  - Timing measurements
- Debounce filter circuitry with flexible edge, level, direction, and debounce settings to better adapt to signals
- Four independent pulse-width modulation (PWM) timers with count, period, delay, and pulse-width registers
- Eight individually-configurable digital I/O channels
- Synchronous high-speed reads of digital and counter inputs
- External clock input and internal clock output
- External digital trigger
- No external power required

### Software

#### Supported Operation Systems


- Windows® 8/7/Vista®/XP 32/64-bit
  - Universal Library (UL), ULx for NI LabVIEW™

#### Ready-to-Run Applications

- InstaCal (install, configure, and test)
- TracerDAQ® (acquire, view, log, and generate)<sup>1</sup>

#### Supported Programming Environments

- Visual Studio® and Visual Studio .NET, including examples for Visual C++®, Visual C#®, Visual Basic®, and Visual Basic .NET
- NI LabVIEW
- DASyLab®



USB-CTR Series includes an 8-channel model (USB-CTR08, shown above) and a 4-channel model (USB-CTR04) that support totalize, period measurement, pulse-width measurement, and timing measurement counter input modes.

### Overview

The USB-CTR Series of high-speed pulse counter/timer devices consists of the USB-CTR08 (eight counter channels) and USB-CTR04 (four counter channels).

Both devices support multiple counting modes and include four PWM timers and eight individually-configurable digital I/O channels.

### Counter I/O and Gating

USB-CTR Series devices support an aggregate throughput rate of 8 MB/s.

These devices can be configured for any resolution up to 64-bits, eliminating the need to cascade counters. Both devices provide the following data streaming rates for these common resolution settings:

- 16-bit: 4 MHz
- 32-bit: 2 MHz
- 64-bit: 1 MHz

Each counter channel on a USB-CTR Series device has a screw terminal connection point for counter input, counter output, and counter gate.

### Counter Inputs

Counter inputs can be read asynchronously under program control, or synchronously with digital inputs as part of a digital scan group. In both cases, counters can be configured to function in one of the following ways:

- counter gets set to 0 after each read
- counter counts up or down and then rolls over at a user-set limit
- counter counts until the user-set limit has been reached

Counter inputs can concurrently monitor time periods, frequencies, pulses, and other event-driven incremental occurrences directly from pulse-generators, limit switches, proximity switches, and magnetic pick-ups.

### Counter Outputs

Counter outputs can be used to control or transmit signals to external devices, and also to counter inputs, counter gates, or digital inputs on a USB-CTR Series device.

### Counter Gates


Counter gates use input signals to clear a counter, change counter direction, or start/stop counting. Gate options are software-selectable.

<sup>1</sup> Supports only timer outputs with the rate generator

# USB-CTR Series

## General Information

USB-CTR Series Block Diagram



## Counter Input Modes

USB-CTR Series devices support the following counter input modes:

- totalize mode (event counter)
- period measurement mode
- pulse-width measurement mode
- timing measurement mode

Counter input modes are software-selectable. Some modes include *max limit* and *min limit* register values. These values do not directly affect the current count, but set limits in some modes to determine counter behavior.

Each mode supports additional counter options.

## Totalize Mode

In totalize mode, a USB-CTR Series device functions as a high speed pulse event counter for general counting applications.

Each counter can be set to any resolution up to 64-bits based on the software-selectable max limit and min limit register values. The counters can accept frequency inputs up to 48 MHz.

The counter input terminal (CxIN) is used as the primary counter input, and the counter gate terminal (CxGT) can be used to perform one of the following functions:

- set the count direction
- gate the counter
- clear/reload the counter with the min limit value
- trigger a particular counter to begin counting.

The following totalize measurement mode options are software-selectable:

**Clear on Read:** The counter is cleared after each read (synchronous or asynchronous). The value of the counter before it was cleared is latched and returned. It is typically cleared to zero, but depending on counting mode, it may be cleared to the value stored in the min limit register.

**Range Limit:** Set max limit and min limit register values to mimic limit switches in a mechanical counter.

- When counting up, the counter freezes or rolls over to the min limit count whenever the count reaches the max limit register value.
- When counting down, the counter freezes or rolls over to the max limit count whenever the count reaches the min limit register value.

# USB-CTR Series

## General Information



**Non-recycle:** The counter freezes if max limit or min limit is reached.

- When counting up, the counter stops when the max limit is reached.
- When counting down, the counter stops when the min limit is reached.

Counting resumes if the direction is reversed or if the counter is reloaded with a value between max limit and min limit.

**CountDown:** Enables count down mode. This mode is overridden by the state of the gate input if the gate is programmed for direction control.

**Output On:** Enables counter output mode. By default, the counter output goes high when the counter reaches the value of output register 0, and low when the counter reaches the value of output register 1.

**Output Initial State:** Sets the initial state of the counter output to either high or low.

**Direction Control:** Allows the counter input terminal (CxIN) to act as the pulse source and the counter gate terminal (CxGT) to act as the direction. By default, the counter increments when CxGT=1 (high), and decrements when CxGT=0 (low).

**Gating:** Allows the counter gate terminal (CxGT) to gate the counter. By default, the counter is enabled when the CxGT signal is high. When the CxGT signal is low, the counter is disabled, but holds the count value.

**Clear/Reload:** Clears the count to zero unless counting in Range Limit mode.

If counting in Range Limit mode, the counter gate signal reloads the counter from the min limit register.

**Count Trigger:** The counter starts counting when the counter gate signal goes active. By default, active is on the rising edge.

### Period Measurement Mode

In period measurement mode, a USB-CTR Series device measures the period of any signal at a counter input (CxIN). The device counts the integral number of *ticks* that make up the period, and the data returned is always time measured in ticks.

The measurement period is the time from edge-to-edge, either both rising or both falling. Period data is latched as it becomes available, and is acquired at the counter read rate.

The data returned is interpreted as time measured in ticks. This data represents the number of tick size intervals counted during the period measurement.

Optionally, the counter gate terminal (CxGT) can be used to gate the counter.

- When **CxGT** is high, the counter is enabled.
- When **CxGT** is low, the counter is disabled, but holds the count value.

The 96 MHz system clock is used as the timing source. Periods from sub-microsecond to many seconds can be measured.

The following period measurement mode options are software-selectable:

**Period mode:** Select one of the following period modes:

- X1 – The measurement is latched each time one complete period is observed.
- X10 – The measurement is latched each time 10 complete periods are observed.
- X100 – The measurement is latched each time 100 complete periods are observed.
- X1000 – The measurement is latched each time 1000 complete periods are observed.

**Tick size:** The tick size is a fundamental unit of time derived from the period of the 96 MHz system clock. Four counter channel tick sizes are available – 20.83 ns, 208.3 ns, 2083.3 ns, and 20833.3 ns.

### Pulse Width Measurement Mode

In pulse width measurement mode, a USB-CTR Series device measures the time from the rising edge to the falling edge, or vice versa, on a counter input signal (CxIN). The measurement is either pulse width low or pulse width high, depending upon the edge detection setting.

Every time the pulse width measurement is latched from the counter, the counter is immediately cleared and enabled to count the time for the next pulse width. The pulse width measurements are latched as they become available.

The data returned is interpreted as time measured in ticks. This data represents the number of tick size intervals counted during the pulse width measurement.

Optionally, the counter gate terminal (CxGT) can be used to gate the counter.

- When **CxGT** is high, the counter is enabled.
- When **CxGT** is low, the counter is disabled, but holds the count value.

The 96 MHz system clock is used as the timing source. Pulse widths from sub-microsecond to many seconds can be measured.

**Tick size:** Refer to the [Tick size](#) description for period mode.

# USB-CTR Series

## General Information




### Timing Mode

In timing mode, a USB-CTR Series device measures the time between an event on the counter input (CxIN) and a subsequent event on the counter gate (CxGT), such as the rising or falling edge of one event with respect to the rising or falling edge of another event (based on the edge detection setting).

Whenever the time measurement is latched from the counter, the counter is immediately cleared and enabled for accepting the subsequent time period, which starts with the next edge on the main channel.

The following example measures the time between the rising edge on a counter input (CxIN) and the falling edge on the counter gate (CxGT). The counter read operation returns zeroes until one complete time measurement has been taken. Then, the time in ticks is latched by the device until the next time measurement has been completed. Rising edges on the counter input channel clear the counter and falling edges on the gate input latch the output of the counter at that time.



Acquired data = 

0000	Time1	Time2
------	-------	-------

Example of a counter input channel in timing mode

The data returned is interpreted as time measured in ticks. This data represents the number of tick size intervals counted during the timing measurement.


**Tick size:** Refer to the [Tick size](#) description for period mode.

### Debounce Filters

USB-CTR Series devices have debounce circuitry which eliminates switch-induced transients that are typically associated with electromechanical devices including relays, proximity switches, and encoders.

All debounce filter options are software selectable. You can select a debounce time, debounce mode, and rising-edge or falling-edge sensitivity. Each channel can be debounced with 16 programmable debounce times in the range of 500 ns to 25.5 ms.

The signal from the buffer can be inverted before it enters the debounce circuitry. The inverter is used to make the input rising-edge or falling-edge sensitive.



Debounce filter modes – trigger after stable and trigger before stable – and a debounce bypass

Edge selection is available with or without debounce. In this case, the debounce time setting is ignored and the input signal goes straight from the inverter or inverter bypass to the counter module.

The two debounce filter modes are *trigger after stable* and *trigger before stable*. In either mode, the selected debounce time determines how fast the signal can change and still be recognized.

### Trigger After Stable Mode


In *trigger after stable* mode, the output of the debounce module does not change state until a period of stability has been achieved. The input has an edge, and then must be stable for a period of time equal to the debounce time.

### Trigger Before Stable Mode

In *trigger before stable* mode, the output of the debounce module immediately changes state, but does not change state again until a period of stability has passed. Use this mode to detect glitches.

### Debounce Filter Mode Comparisons

The following diagram shows how the two modes interpret the same input signal, which exhibits glitches. Notice that the trigger before stable mode recognizes more glitches than the trigger after stable mode. Use the *bypass* option to achieve maximum glitch recognition.



Example of two debounce filter modes interpreting the same signal



# USB-CTR Series

## General Information



*Trigger after stable* mode behaves more like a traditional debounce function: rejecting glitches and only passing state transitions after a required period of stability. *Trigger after stable* mode is used with electromechanical devices like encoders and mechanical switches to reject switch bounce and disturbances due to a vibrating encoder that is not otherwise moving.

## Digital I/O

USB-CTR Series devices can connect up to eight digital I/O lines. The digital I/O terminals can detect the state of any TTL-level input.

## Pull-Up/Down Jumper

The digital port has 47 k $\Omega$  resistors that you can configure as pull-up or pull-down with internal jumper.

Unconnected inputs are pulled low by default to 0 V through 47 k $\Omega$  resistors. The pull-up/down voltage is common to all of these resistors.

## Synchronous Counter and Digital Inputs

USB-CTR Series devices can read digital and counter inputs simultaneously at the supported data streaming rates (refer to [Counter I/O and Gating](#)).

## Timer Output


USB-CTR Series devices have four 32-bit timer outputs. Each timer can generate a programmable width pulse with a software-selectable frequency in the range of 0.02235 Hz to 48 MHz. At higher frequencies, the timer output frequency and duty cycle depend on the load impedance and the supply.

The timer output rate and pulse width can be updated asynchronously at any time; however, doing so results in a pulse stream that is not seamless.

The following timer output options are software-selectable:

- pulse frequency
- duty cycle (pulse width divided by the pulse period)
- number of pulses to generate
- time delay before starting the timer output after it's enabled
- resting state of the output (*idle high* or *idle low*)

Both the period and time delay ranges are 20.83 ns to 44.739 seconds.



USB-CTR Series PWM timer channel

## Trigger Input

USB-CTR Series devices can trigger synchronous acquisitions of counter data internally with software or externally using the digital trigger input screw terminal.

The digital trigger input allows TTL-level triggering with latencies guaranteed to be less than 20.83 ns. The acquisition can be triggered on a rising or falling edge, or on a high or low level. The trigger input is TTL logic. Latency is one sample period, maximum. The input signal range is -0.5 V to 5.5 V maximum. The logic level (1 or 0) and the rising or falling edge for the discrete trigger input are software-selectable.

When using the external trigger, the counter begins counting when the scan starts, even though acquisition of the count is held off by the trigger. To coordinate the start of the acquisition with the start of the count, you could use the trigger signal to also trigger the gate of the counter in use. Clearing the counter before starting the scan re-arms the gate trigger.

## External Clock Pacing

You can pace synchronous acquisition of counter data by the onboard clock or by an external clock connected to the external clock input terminal.

## Power Output

The total supply current at the power output (+VO) terminal is 240 mA, maximum, including DIO. You can use the +VO terminal to supply power to external devices or circuitry.

The maximum total output current that can be drawn from all USB-CTR Series device connections (counter outputs, timer outputs, digital outputs, pacer clock output, and +VO) is 240 mA. This maximum applies to most personal computers and self-powered USB hubs. Bus-powered hubs and notebook computers may limit the maximum available output current to 100 mA.

If the current requirement of the device exceeds the current available from the computer, connect to a self-powered hub or power the computer with an external power adapter.

# USB-CTR Series

## General & Software Information



### Software Support

USB-CTR Series devices are supported by the software in the table below.

Ready-to-Run Applications		
<a href="#">InstaCal™</a>		An interactive utility that configures and tests MCC hardware. Windows® OS  InstaCal is included with the free MCC DAQ Software bundle (CD/download).
<a href="#">TracerDAQ® and TracerDAQ Pro</a> (Supports only timer outputs with the rate generator)		A virtual strip chart, oscilloscope, function generator, and rate generator applications used to generate, acquire, analyze, display, and export data. The Pro version provides enhanced features. Windows OS  TracerDAQ is included with the free MCC DAQ Software bundle (CD/download). TracerDAQ Pro is available as a purchased software download.
General-Purpose Programming Support		
<a href="#">Universal Library (UL)</a>		Programming library of function calls for C, C++, VB, C# .Net, and VB .Net using Visual Studio and other IDEs. Windows OS  The UL is included with the free MCC DAQ Software bundle (CD/download).
Application-Specific Programming Support		
<a href="#">ULx for NI LabVIEW™</a>		A comprehensive library of VIs and example programs for NI LabVIEW that is used to develop custom applications that interact with most MCC devices. Windows OS  ULx is included with the free MCC DAQ Software bundle (CD/download).
<a href="#">DASYLab® Driver</a>		Icon-based data acquisition, graphics, control, and analysis software that allows users to create complex applications in minimal time without text-based programming.  DASYLab is available as a purchased software download. Windows OS

### Specifications

All specifications are subject to change without notice.  
Typical for 25°C unless otherwise specified.

#### Counter

**Counter Type:** FPGA

##### Counters

USB-CTR08: 8

USB-CTR04: 4

Each counter channel has a corresponding Input, Gate, and Output connector

**Counter Input Modes:** Totalize, Pulse width, Period, Timing

**Mode Options:** Non-Recycle, Range Limit, Clear on Read, Up/Down

**Gate Options:** Clear/Reload, Direction Control, Gate, Count trigger; mode dependent

**Resolution:** Up to 64-bits (software-selectable)

**Maximum Input Frequency:** 48 MHz

**Debounce Times:** 16 steps from 500 ns to 25.5 ms; positive or negative edge sensitive; glitch detect mode or debounce mode; software-selectable.

**Timebase and Accuracy:** 96 MHz (24 MHz – 30 ppm with a 4x DLL (delay-locked loop))

**Counter Read Pacer:** Internal or external scan pacer up to 4 MHz

**Period/Pulse Width Resolution:** 20.83 ns; 208.3 ns; 2.083 µs; or 20.83 µs

**Input Type (Counter Input and Gate Terminals):** Schmitt trigger, 47 kΩ pull-down to ground with 33 Ω in series

**Schmitt Trigger Hysteresis (C0IN To C7IN and C0GT To C7GT):** 0.76 V typ, 0.4 V min, 1.2 V max

**Input High Voltage Threshold (C0IN To C7IN and C0GT To C7GT):** 1.74 V typ, 1.3 V min, 2.2 V max

**Input High Voltage Limit (C0IN To C7IN and C0GT To C7GT):** 5.5 V absolute max

**Input Low Voltage Threshold (C0IN To C7IN and C0GT To C7GT):** 0.98 V typ, 0.6 V min, 1.5 V max

**Input Low Voltage Limit (C0IN To C7IN and C0GT To C7GT):** –0.5 V absolute min, 0 V recommended min

**Output High Voltage:** 4.4 V min (IOH = –50 µA); 3.76 V min (IOH = –24 mA)

**Output Low Voltage:** 0.1 V max (IOL = 50 µA); 0.44 V max (IOL = 24 mA)

**Output Current:** 24 mA max per pin, constrained to 240 mA across all output pins (counter outputs, timer outputs, digital outputs, pacer clock output, and +VO)

#### Timers

**Terminal Names:** TMR0, TMR1, TMR2, TMR3

**Timer Type:** PWM output with count, period, delay, and pulse width registers  
**Output Value:** Default state is idle low with pulses high, software-selectable output invert

**Internal Clock Frequency:** 96 MHz

**Effective Frequency Range:** 0.022 Hz to 48 MHz

**Register Widths:** 32-bit

**High Pulse Width:** 10.42 ns min

**Low Pulse Width:** 10.42 ns min

**Output High Voltage:** 4.4 V min (IOH = –50 µA); 3.76 V min (IOH = –24 mA)

**Output Low Voltage:** 0.1 V max (IOL = 50 µA); 0.44 V max (IOL = 24 mA)

**Output Current:** 24 mA max per pin, constrained to 240 mA across all output pins (counter outputs, timer outputs, digital outputs, pacer clock output, and +VO)

# USB-CTR Series

## Specifications



### Digital Input/Output

**Digital Type:** TTL

**Number Of I/O:** 8

**Configuration:** Bit-configurable as input (power on default) or output

**Pull-Up Configuration:** The port has a 47 k $\Omega$  resistor configurable as a pull-up or pull-down (default) with an internal jumper.

**Digital I/O Transfer Rate (System-Paced, Asynchronous):** 33 to 8000 port reads/writes or single bit reads/writes per second typical, system dependent.

**Digital Input Pacing:** Onboard clock, external input scan clock (CLKI)

**Digital Input Trigger Source:** External single channel digital trigger (TRIG)

**Input High Voltage:** 2.0 V min, 5.0 V absolute max

**Input Low Voltage:** 0.8 V max, 0 V recommended min

**Output High Voltage:** 4.4 V min (IOH = -50  $\mu$ A)  
3.76 V min (IOH = -24 mA)

**Output Low Voltage:** 0.1 V max (IOL = 50  $\mu$ A)  
0.44 V max (IOL = 24 mA)

**Output Current:** 24 mA max per pin, constrained to 240 mA across all output pins (counter outputs, timer outputs, digital outputs, pacer clock output, and +VO)

### External Trigger

**Trigger Source:** External digital; TRIG terminal

**Trigger Mode:** Software-selectable for edge or level sensitive, rising or falling edge, high or low level.

**Trigger Latency:** 100 ns max

**Trigger Pulse Width:** 100 ns min

**Input Type:** Schmitt trigger, 47 k $\Omega$  pull-down to ground with 33  $\Omega$  in series

**Schmitt Trigger Hysteresis:** 0.76 V typ, 0.4 V min, 1.2 V max

**Input High Voltage Threshold:** 1.74 V typ, 1.3 V min, 2.2 V max

**Input High Voltage Limit:** 5.5 V absolute max

**Input Low Voltage Threshold:** 0.98 V typ, 0.6 V min, 1.5 V max

**Input Low Voltage Limit:** -0.5 V absolute min, 0 V recommended min

### External Clock Input/Output

**Terminal Names:** CLKI, CLKO

**Terminal Type**

CLKI: Input, active on rising edge

CLKO: Output, power on default is 0 V, active on rising edge

**Input Clock Frequency:** 4 MHz, max

**Input Clock Pulse Width:** 10.417 ns min

**Input Type:** Schmitt trigger, 47 k $\Omega$  pull-down to ground with 33  $\Omega$  in series

**Input Schmitt Trigger Hysteresis:** 0.76 V typ, 0.4 V min, 1.2 V max

**Input High Voltage Threshold:** 1.74 V typ, 1.3 V min, 2.2 V max

**Input High Voltage Limit:** 5.5 V absolute max

**Input Low Voltage Threshold:** 0.98 V typ, 0.6 V min, 1.5 V max

**Input Low Voltage Limit:** -0.5 V absolute min, 0 V recommended min

**Output Clock Frequency:** 4 MHz, max

**Output Clock Pulse Width:** 10.417 ns

**Output High Voltage:** 4.4 V min (IOH = -50  $\mu$ A), 3.78 V min (IOH = -24 mA)

**Output Low Voltage:** 0.1 V max (IOL = 50  $\mu$ A), 0.44 V max (IOL = 24 mA)

**Output Current:** 24 mA max per pin, constrained to 240 mA across all output pins (counter outputs, timer outputs, digital outputs, pacer clock output, and +VO)

### Memory

**FIFO:** 8 KS

**Non-Volatile EEPROM:** 32 KB (10 KB firmware storage, 22 KB calibration/user data)

### Power

**Supply Current, USB Source**

**During Enumeration:** < 100 mA

**After USB Enumeration:** < 500 mA

**+VO Power Available:** After USB enumeration: 5 V,  $\pm$  5%

**+VO Output Current:** After USB enumeration: 24 mA max per pin, constrained to 240 mA across all output pins (counter outputs, timer outputs, digital outputs, pacer clock output, and +VO)

### USB

**USB Device Type:** USB 2.0 (high-speed)

**Device Compatibility:** USB 1.1, USB 2.0, USB 3.0

**USB Cable Type:** A-B cable, UL type AWM 2725 or equivalent. (min 24 AWG VBUS/GND, min 28 AWG D+/D-)

**USB Cable Length:** 3 m (9.84 ft) max

### Environmental

**Operating Temperature Range:** 0  $^{\circ}$ C to 50  $^{\circ}$ C

**Storage Temperature Range:** -40  $^{\circ}$ C to 70  $^{\circ}$ C

**Humidity:** 0% to 90% non-condensing

### Mechanical

**Dimensions (L  $\times$  W  $\times$  H):** 127  $\times$  89.9  $\times$  35.6 mm (5.00  $\times$  3.53  $\times$  1.40 in.)

**User Connection Length:** 3 m (9.84 ft) max

### Signal Connector

**Connector Type:** Screw terminal

**Wire Gauge Range:** 16 AWG to 30 AWG

## Ordering Information

Part No.	Description
USB-CTR08	High-speed counter/timer device with 8 counter I/O, 4 PWM timer outputs, and 8 digital I/O (includes USB cable and MCC DAQ software CD)
USB-CTR04	High-speed counter/timer device with 4 counter I/O, 4 PWM timer outputs, and 8 digital I/O (includes USB cable and MCC DAQ software CD)

## Software

Part No.	Description
TracerDAQ Pro	Out-of-the-box virtual instrument suite with strip chart, oscilloscope, function generator, and rate generator – professional version
DASYLab	Icon-based data acquisition, graphics, control, and analysis software